




NOTES

Pieces assembly
Packaging : per 100 pieces
Material : steel
Plating : tin
Thread : UNC 4.40

ASSEMBLY VIEW





Part number	863015ATLF

European Views

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	BART	2004/02/26	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 5
Eng	PESSON	2004/02/26			0.XX	±0.1		
Chr	ABHILASH	2011/01/25	0.XX°	±2°	0.XXX	±0.1	ECN	ELX–H–011686
Appr	SUDHIR	2011/01/25	Product family			D–SUB	Spec ref	–

title	MALE SCREW LOCKS SHELL 50 D SUB ACCESSORIES	dwg no	C01–8655–1588	Rev. G
	catalog no –		CUSTOMER	sheet 1 of 1

NOTE: RoHS INFORMATIONS

- The "LF" products meet European union Directives and other country regulations as described in GS–22–008.
- Plating Sn (pure bright) over copper
- Packaging spec: see GS–14–920

rev	ecn no	dr	date
A	–	BAR	2004/02/26
B	LS05–0026	MPE	2005/07/08
C	LS06–0097	LGO	2006/07/28
D	LS09–0006	PCR	2009/01/08
E	I11–0022	AMR	2011/01/25
F	ELX–H–011663	PK	2012/05/09
G	ELX–H–011686	PK	2012/05/21

REV F – 2006–04–17

Copyright FCI.
PDS: Rev :G STATUS:Released Printed: May 22, 2012
Downloaded from Arrow.com