

Modular connectors




Modular plug, 6p6c (RJ12), with locking latch, piercing technology

Downloaded from Arrow.com.



*a



*a piercing contact

Environmental conditions

Temperature range	-40 °C/+125 °C

Materials

Insulating body	PC, V-2 according to UL94
Contact	CuSn, gold-plated

Connectable conductors for piercing area

Section	AWG 26–24, 0.128–0.241 mm²
Construction	flat cable
Stripping length cable jacket	6 mm

Electrical data (at T_{amb} 20 °C)

Rated current	1.5 A
Rated voltage	250 V AC
Insulation resistance	500 MΩ

Associated products

Counterparts

Downloaded from Arrow.com.

Harnessing equipment

ZP25-2 ZP25-3

Downloaded from Arrow.com.

25 P 128

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
P 128	6	1000	3000

Packaging:
in bulk, in a cardboard box or a plastic bag

Downloaded from Arrow.com.