



SYM	ECN	DESCRIPTION	DATE	APPROVED
0A	---	FIRST RELEASE	08/01'24	Dam



LABEL:




NOTES:

- PRODUCT MUST COMPLY TO THE LATEST LEVEL OF SAE/USCAR30.
- ELECTRICAL PERFORMANCE:
CURRENT RATING: 5A
INSULATION RESISTANCE: 5MΩ MIN. (200V DC)
- MECHANICAL PERFORMANCE:
DURABILITY: 10 CYCLES MIN.
TEMPERATURE RANGE: -40°C TO +105°C
- MATERIAL SHOULD BE FULFILLED RoHS REQUIREMENT AND AMPHENOL SPEC# SSN002.
- ORDER P/N SYSTEM:

USBCC 23 1 AA 0 19 AS
USBC CABLE
23: MINI HSBridge+
1: 5G
AA: CODE A TO CODE A
CUSTOMER CODE
SEQUENCE
RESERVED

WIRE LIST:



HF(无卤)	
Non-HF(有卤)	✓

3	CONNECTOR	MINI HSBRIDGE+ USBC INLINE CABLE CONNECTOR CODE-A	1
2	CONNECTOR	MINI HSBRIDGE+ USBC PLUG CABLE CONNECTOR CODE-A	1
1	RAW CABLE	USB3.1 FEP,(30AWG-1P+EAM)×4+(30AWG-1P+AM)×(32AWG-1C)×4+21AWG×1C,005.2	A/R
ITEM	NAME	DESCRIPTION	QUANTITY
UNLESS OTHERWISE SPECIFIED TOLERANCES			
U.S.		APPROVAL	DATE
0 +/-		DRAWN Simon	08/01'24
0.00 +/-		CHECKED Johnny	08/01'24
FRACTIONS +/-		CHECKED	
ANGLES +/-			
FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES			
DIMENSIONS		ANGLE OF PROJECTION	
U.S. INCHES			
(METRIC) (MM)			
TITLE			
Amphenol			
Amphenol East Asia Limited			
CUSTOMER DRAWING FOR MINI HSBRIDGE+ USBC PLUG TO INLINE CABLE, CODE A-A, L=200MM			
SIZE	DRAWING NO.	REV.	
A3	USBCC231AA019AS	0A	
SCALE	N/A	SHEET	1 OF 1