

Search within category

GO

BUY NOW

DESIGN / INSTALL



UTP28SP5OR

Category 6 Performance, 28 AWG UTP patch cord with TX6™ Modular Plugs on each end.

Specs

Documents

★ Add to Favorites

Add to BOM

Std. Pkg. Qty.	1
Product Type	Copper Patch Cord
Performance Level	Category 6/Class E
Cable Type	U/UTP
Cable Color	Orange
Length (ft.)	5.00
Length (m)	1.5
Flammability Rating	Dual Rated (CM/LSZH)
Termination End 1	Modular Plug
Termination End 2	Modular Plug
Standards	PoE,PoE+
Wiring Scheme	T568B
CE Compliant	Yes
Nominal Cable O.D. (In.)	0.15
Nominal Cable O.D. (mm)	3.8
Operating Temperature	14°F to 140°F (-10°C to 60°C)
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
UL5A Listed	-
Conductor Material	Copper
Temperature Rating	14°F to 140°F (-10°C to 60°C)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

Back to Top