

NOTES:

1. FINISHED CABLE ASSEMBLY TO BE COILED
2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHEN NOTED WITH TOLERANCE

ASS'Y P/N	NO. OF POS.
CARA162802PPXXX90	2
CARA162803PPXXX90	3
CARA16280XPPXXX90	



CABLE LENGTH IN "INCHES"

NO. OF POSITIONS


ASS'Y P/N	"X" DIM.
CARA162802PP03990	3 FT. 3 1/2 IN. ± 2 IN. [1M ±50.8mm]
CARA162803PP03990	6 FT. 7 IN. ± 2 IN. [2M ±50.8mm]
CARA162802PP07990	16 FT. 5 IN. ± 4 IN. [5M ±101.6mm]
CARA162803PP19790	32 FT. 9 3/4 IN. ± 8 IN. [10M ±203.2mm]
CARA16280XPPXXX90	

CABLE LENGTH IN "INCHES"

NO. OF POSITIONS



ASSY P/N	CABLE	COLOR CODE END "A"
CARA162802PPXXX90	2/20 AWG O.D. 0.215 REF	COLOR CODE POS. 1 POS. 2 BLK WHT
CARA162803PPXXX90	3/20 AWG O.D. 0.220 REF	WIRE COLOR CODE POS. 1 POS. 2 POS. 3 BLK WHT GRN



END "A"
FACE VIEW
CARA162803PPXXX90

DIMENSIONS IN BRACKETS [] ARE METRIC

CUSTOMER APPROVAL		
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.		
APPROVED BY: _____		
DATE: _____		

RoHS COMPLIANT

A	AN	06-08-21	DRAWING CREATED PER DOR 21-109360DS		
REV.	INIT.	DATE	DESCRIPTION		
ORIG. DRAWN BY: DATE: AN 06-08-21			CHECKED BY:		
APPROVED BY:			APPROVED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			SCALE	SIZE	SHEET
			NTS	B	1 OF 1
			TITLE: CABLE ASSEMBLY (2-3) #20 PIN CONTACTS INSTA-CLICK™ MICRO-CON-X STANDARD PRODUCT		
			FILE: CARA16280XPPXXX90 DIRECTORY: SLW		
			PART NUMBER: CARA16280XPPXXX90 REV A		

CONXALL
601 E. WILDWOOD VILLA PARK, IL 60181