



**Part Number :** 1301530028  
**Product Description :** Safeway In-Line  
Commercial GFCI, Permanent Mount, Single  
Phase, Manual Reset, Molded NEMA 5-15 Tri-  
Tap, 15A, 120V, 0.61m (2.0') Cord Length  
**Series Number :** 130153  
**Status :** Active  
**Product Category :** Power Distribution  
**Engineering Number :** 15050-3TT



Documents & Resources

Drawings  
1301530028\_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Power Distribution
Series	130153
Description	Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Molded NEMA 5-15 Tri-Tap, 15A, 120V, 0.61m (2.0') Cord Length
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Safeway
Type	GFCI Commercial Duty, Single Phase
UPC	78678828428

### Agency

CSA	LR6837
UL	E66308

### Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V AC

### Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Cord Type	N/A
Feed-Thru	Yes

Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Net Weight	566.990/g
Number of Receptacles	3
Packaging Type	Bag
Receptacle Type	N/A

---

This document was generated on Apr 22, 2025

---