



Part Number : [190700069](#)

Product Description : InsulKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 5-6 (M3-3.5), Length 19.94mm, Blue, Carton

Series Number : 19070

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : BB-223-06X

Documents and Resources

Drawings

[190700069 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19070
Description	InsulKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 5-6 (M3-3.5), Length 19.94mm, Blue, Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753069220

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Blue

Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.500/g
Packaging Type	Carton
Stud Size	5-6 (M3-3.5)
Wire Insulation Diameter	4.40mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 22-10 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050300</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>

This document was generated on May 20, 2026