





1. NOTE DELETED.
2. MOLDED PARTS: FLAME RETARDANT 94V-O RATED THERMOPLASTIC; COLOR, BLACK
CONTACT: BRASS
SHELLS: STEEL
3. GOLD FLASH FOR A LENGTH OF .150 MIN FROM MATING END .000100 MIN TIN-LEAD ON OPPOSITE END, ALL OVER 1.27 MIN NICKEL.
4. GOLD PLATED FOR A LENGTH OF .150 FROM MATING END, .000030 MIN GOLD IN MATED AREA, .000100 MIN TIN-LEAD ON OPPOSITE END, ALL OVER .000050 MIN NICKEL.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL PLATED FOR LENGTH OF .150 MIN FROM MATING END, .000030 MIN TOTAL IN MATED AREA, .000100 MIN TIN-LEAD ON OPPOSITE END, ALL OVER .000050 MIN NICKEL.
5. .000200 MIN TIN OVER .000100 MIN COPPER.



SUPSD BY 745412-7	3	.188	745412-8
	4	.188	745412-7
OBSOLETE	3	.651	745412-6
SUPSD BY 745412-1	4	.651	745412-5
SUPSD BY 205737-4	3	.427	745412-4
SUPSD BY 205737-3	4	.427	745412-3
SUPSD BY 745412-1	3	.125	745412-2
	4	.125	745412-1
CONTACT FINISH		DIMENSION A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.GERACE 10-25-83	 Tyco Electronics Corporation Harrisburg, PA 17105-3608							
		CHK J.GERACE 10-25-83								
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD B. TAYLOR 1-04-84	NAME			PLUG ASSEMBLY, SIZE 3, 25 POSN, VERTICAL, .025 SQ. POSTS, W/ GROUNDING INDENTS, AMPLIMITE™HDP				
		PRODUCT SPEC 108-40025								
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APPLICATION SPEC 114-40013	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
	MATERIAL	FINISH	WEIGHT	A2 00779 C-745412				-		
	SHELLS: 	CUSTOMER DRAWING			SCALE	N TS	SHEET	1 of 1	REV	K
CONTACTS: SEE TABLE										