

## Data Sheet | Item Number: 249-619

WSB marking card; as card; MARKED; F41, ..., F50 (10x); not stretchable; Vertical marking; snap-on type; white

<https://www.wago.com/249-619>



Color: ■ white

Similar to illustration

### Technical data

Marking method	Thermal transfer
Marking	F41, ..., F50
Marking (number)	10
Marking direction	Vertical marking
Marking color	black
Marking type	Symbol
Marking layout	Consecutive symbols each strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2

### Physical data

Height	152 mm / 5.984 inches
Width	46.4 mm / 1.827 inches
Depth	3 mm / 0.118 inches
Marker/strip width	5 mm
Marker width	5 mm

### Mechanical data

Smear resistance	EN 60998-1:2004
------------------	-----------------

**Material data**

Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	7.8 g
Fire load	0.234 MJ

**Commercial data**

Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332134484
Customs tariff number	49119900000

**Product Classification**

UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 10.0	EC000761
ECCN	NO US CLASSIFICATION

**Environmental Product Compliance**

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

**Downloads****Environmental Product Compliance****Compliance Search**Environmental Product  
Compliance 249-619