

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0734151692
Status: Active
Overview: MCX RF Connectors
Description: 50 Ohms, MCX Vertical Surface Mount Jack Receptacle, 0.02µm Gold (Au) Plated Body, Tape and Reel

Documents:

[3D Model](#)
[3D Model \(PDF\)](#)
[Drawing \(PDF\)](#)
[Product Specification PS-89675-183-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family RF/Coax Connectors
Series 73415
Overview MCX RF Connectors
Product Name MCX
Style PCB
Taxonomy RF / Coaxial Connectors
Type Microminiature
UPC 800755980912
Wire/Cable Type N/A

Physical

Gender Jack
Keying to Mating Part None
Net Weight 0.509/g
Orientation Straight
PCB Mounting Surface Mount
Packaging Type Embossed Tape on Reel
Panel Mount No
Panel Mount Method N/A
Reverse Polar No

Electrical

Frequency 6 GHz
Impedance 50Ω
Power / Voltage VOLTAGE: 335 Vrms@Sea Level

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
Lead-freeProcess Capability REFLOW
Max. Cycles at Max. Process Temperature 002
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Product Specification PS-89675-183-001
Sales Drawing SD-73415-169-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

73415 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION