



Part Number : [734152240](#)

Product Description : MCX Plug, Straight, Crimp, RD-316 Cable, Die Cast Body, Gold (Au) Plated, 50 Ohms

Series Number : 73366

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[734152240 sd.pdf](#)


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Plug, Straight, Crimp, RD-316 Cable, Die Cast Body, Gold (Au) Plated, 50 Ohms
Application	RF
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	800753289949

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	1.544/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A

PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-316 Double Shielded

This document was generated on Dec 29, 2025