

Chloroprene tubing and grommets H30X25BK

Helsyn H, Article number: 600-02938



Images (3)

Downloads



Features

- Highly elastic, easy to fit chloroprene tubing
- Withstands up to 120 °C intermittent temperature
- Covers many cable diameters with one size
- Available in cut lengths

Certifications & Approvals

RoHS

BS

DEF STAN

Application

The chloroprene tubings are ideally suited to rigorous environments such as the automotive, aerospace, mass transit and defence markets.

As the material is highly elastic, it's original size can be expanded 500% on application and 200% in continuous use.

To save time and effort when fitting the tubings, try the HellermannTyton NA three prong tools and the Hellerine lubricant, which are specially designed for use with HellermannTyton chloroprene tubing.

Helsyn H is suitable for following markets and industries

Automotive Industry

Electronics Industry

More products in this product group

[Chloroprene tubing and grommets >](#)

Base Data

Application Tool	VA2.5/5, NA1K/3
Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	Chloroprene Rubber Tubing 25x3mm black
Pack Cont.	1000 pcs.
Package Quantity per	bag
PART DESCRIPTION	H30X25BK-CR-BK
Product Family	Helsyn H
Product Group	Chloroprene tubing and grommets

Product Dimensions



Bundle ∅ max.	6.0 mm
Inside Ø (ID)	3.0 mm
Length (L)	25.0 mm
Supplied ∅ D min.	3.0 mm
Wall (WT)	0.80 mm

Material and Specifications



Elongation at break	min. 500%
ELV compliant (Article 4 - 2)	YES
Flammability	UL 94 HB
Hazardous good	No
Material	Chloroprene Rubber (CR)
Operating Temperature - °C	-65 °C to +95 °C, intermittent +120 °C
Specifications	  
Specifications	BS-4G-198 Part 1 Type 1, DEF STAN 59-15 D2

Logistics and Packaging



More Information



ETIM 6.0	EC002254
----------	----------

Further information to H30X25BK



 Catalogue page (December 2017)	 All catalogue pages More information >	 Technical drawing 15-0206-001-CSG Download >	 Technical drawing 15-0206-002-CSG Download >
---	---	---	---

You can easily accept or reject the cookies on this site by choosing one of the following links:
[statement](#)

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

