

Specification Sheet

Part Number: 133-02808



One-piece design allows installers to mount and bundle wire or cables single-handedly.

Wing design helps stabilize the tie in high vibration applications.

1-Piece Cable Tie with Fir Tree Mount with Wings, 6.8 Long, 0.25 - 0.28" Hole Dia, PA66HIRHS, Blk, 2400/ctn

Article Number	133-02808
Type	T50RFT6.5EXLG
Color	Black (BK)
Quantity Per	carton
Product Description	One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. Wing design helps stabilize the tie in high vibration applications.
Short Description	1-Piece Cable Tie with Fir Tree Mount with Wings, 6.8 Long, 0.25 - 0.28" Hole Dia, PA66HIRHS, Blk, 2400/ctn
Global Part Name	T50RFT6.5EXLG-PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.77
Length L (Metric)	171.9
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Width W (Imperial)	0.19
Width W (Metric)	4.8
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Height H (Imperial)	1.13

Height H (Metric)	28.6
Panel Thickness Min (Imperial)	0.25
Panel Thickness Max (Imperial)	0.83
Panel Thickness Min (Metric)	6.3
Panel Thickness Max (Metric)	21.0
Mounting Hole Diameter D (Imperial)	0.25 - 0.28 "
Mounting Hole Diameter D (Metric)	6.3 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	2400
Package Quantity (Metric)	2400
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)