






NOTES:

- | | | |
|---|---|--|
| ① | MATERIAL HOUSING | : GREY GLASSFILLED POLYESTER
UL-RATING V0 |
| ② | CONTACT | : PHOSPHORBRONZE |
| ③ | GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER. | |
| ④ | CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2. | |
| ⑤ | CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR. | |
| ⑥ | CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE | |
| ⑦ | PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID. | |
| ⑧ | AREA FOR KEYING PART (BASIC PART NUMBER 100525). | |

CONTACT DIMENSIONS




RECOMMENDED PCB-HOLE LAY-OUT
COMPONENT SIDE SHOWN



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE APPLICATION SPECIFICATION

CONTACT LAYOUT



188395

B

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		C	EHCO-0195-04	06-07-04	DvdB	BM
			D	EH10-0680-05	06-06-05	BSV	BM
			D1	ECR-06-002635	07-02-06	BSV	BM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.v.d.HEIJDEN 15DEC97		tyco Tyco Electronics Corporation s-Hertogenbosch, Netherlands,									
		CHK D. TRUREN 15DEC97											
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Z-PACK 2MM HM TYPE A 110 POS. RIGHT ANGLE MALE CONNECTOR ASSEMBLY									
		APPROVED F.v.KONINGSBRUGGE PRODUCT SPEC											
		APPLICATION SPEC											
		114-19029											
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
-		-		A2	00779	C-188395	-						
CUSTOMER DRAWING						SCALE	NTS	SHEET	1	OF	1	REV	D1