




REV.	DESCRIPTION	DATE	APPROVED
F	Added Note 4	06/19/09	T. Y.
G	Updated Note 4 with Table 3	07/27/10	T. Y.
H	Remove PPS and GF30 Material	11/02/11	T. Y.
J	Removed Material Code	05/28/16	J. C.



PART NO.	DIA
H-100C	.132 (3.4mm)
H-100C-1	.150 (3.8mm)
H-101C	.132 (3.4mm)
H-101C-1	.150 (3.8mm)
H-102C	.132 (3.4mm)
H-102C-1	.150 (3.8mm)
H-103C	.132 (3.4mm)
H-103C-1	.150 (3.8mm)



2. MATERIAL 1: NYLON 6/6, 94V-0, BLACK.

1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°	 TITLE: T-1 (3mm) LED HOLDER, 90° MOUNT INTERLOCKING VARIABLE DIAMETER	
.XX ± .01			
.XXX ± .005			
DESIGNED:	DATE:	PART NO:	REVISION:
M. Chen	01/21/03	H-10XC-X	J
CHECKED:	DATE:	CAGE CODE : 32559	SHEET # 1 OF 1
D. Green	01/21/03	CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.	