



Part Number : [135220001](#)
Product Description : Dual Frequency RFID Label,
16.8mm HF / 2.4m UHF Read Range, 50.00 by
30.00mm Footprint, For Non-Metal Surfaces, Adhesive
Attachment
Series Number : 13522
Status : Active
Product Category : Asset Tracking

Documents & Resources

Drawings
[135220001 sd.pdf](#)
Specifications
[135220001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Asset Tracking
Series	13522
Description	Dual Frequency RFID Label, 16.8mm HF / 2.4m UHF Read Range, 50.00 by 30.00mm Footprint, For Non-Metal Surfaces, Adhesive Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Non-Metal Surfaces
UPC	196823496127

Electrical

Frequency	860-960 MHz UHF, 13.56 MHz HF
-----------	-------------------------------

Physical

Length	50.0mm
Mounting Style	Adhesive
Packaging Type	Roll
Read Range	2.4m UHF, 16.8mm HF
Thickness	0.254mm
Width	30.0mm