Specification Sheet

Part Number: 151-02741



Standoff design secures the bundle away from the mounting hole and below the mounting surface.

Fir tree design provides low insertion force and high extraction force ideal for simple, secure performance.

Secure into wide range of panel thicknesses up to 6.1 mm.

Standoff Bundling Clip, 1.6" Long, Panel Thickness 0.6-6.1 mm, PA66HIRHSUV, Black, 2000/carton

Article Number	151-02741
Type	SOC18OS-21FT6.5
Color	Black (BK)
Quantity Per	pack
Product Description	Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.
Short Description	Standoff Bundling Clip, 1.6" Long, Panel Thickness 0.6-6.1 mm, PA66HIRHSUV, Black, 2000/carton
Global Part Name	SOC18OS-21FT6.5-PA66HIRHSUV-BK

Downloaded from Arrow.com.

Length L (Imperial)	1.57
Length L (Metric)	40.0
Offset Length (Imperial)	0.708
Offset Length (Metric)	18.0
Width W (Imperial)	1.03
Width W (Metric)	26.2
Height H (Imperial)	0.976
Height H (Metric)	24.8
Mounting Hole Diameter D (Imperial)	0.24 - 0.28 "
Mounting Hole Diameter D (Metric)	6.1 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	6.9

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Downloaded from Arrow.com.

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature intermittant, 1000 hours	+320°F (+160°C)
Operating Temperature intermittant, 5000 hours	+257°F (+125°C)
Operating Temperature intermittant, 500 hours	+329°F (+165°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.