Part Number : 2204240010
Product Description : Squba Weather Cap for 10 Circuit Receptacle Housing
Series Number : 220424
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

2204240010_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2042200000-AS-000.pdf

2077760000-AS-000.pdf

2042200000-PS-000.pdf

2042200000-TS-000.pdf

2077760000-PS-000.pdf

2077760000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	220424
Description	Squba Weather Cap for 10 Circuit Receptacle Housing
Component Type	Cap
Keyword	Squba 1.8
Product Name	Squba
UPC	196823073793

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Polyamide (PA)
Net Weight	1.260/g
Packaging Type	Bag

Downloaded from Arrow.com.

Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Squba 1.8 Sealed Single Row Receptacle Assemblies	204220
Squba 3.6 Sealed Single Row Receptacle Assemblies	207782

Downloaded from Arrow.com.