



YAE18G43F

by Burndy
Catalog ID: YAE18G43F

Prop 65 Notice

Terminal - Nylon Insulated, Multi-Finger Insulation Grip, Fork Tongue, 22 AWG - 16 AWG, AN22-AN16, #4-#6 stud, Electro Tin Plated, Bulk Packaging

Product Details

General

Application	Power Connector
Color Code	Red
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork Terminal
Plated	Y
Plating Type	Electro Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810804612
UPC 12 Digit	7818108046122

Dimensions

Dimension - B Length fraction	5/32 in
Dimension - B Length inch	0.16 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.78 in
Dimension - N inch	0.09 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.18 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18;AN 16
Conductor - Copper Str Aircraft Size Range	AN 22-AN 16
Conductor - Copper Str Size Range	22 AWG - 16 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	- UL486 - Military Specified (Mil-Spec)
Standards - Industry Standards Met	- UL486 - Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)