

Data Sheet | Item Number: 209-998

WSB marking card; as card; MARKED; A1, A2, A1, A2, RL, -, , RL, - , ;

Vertical marking; snap-on type; white

<https://www.wago.com/209-998>



Color: ■ white

Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	A1, A2, A1, A2, RL, -, , RL, - , ;
Marking (number)	10
Marking direction	Vertical marking
Marking color	black
Marking type	Symbol
Marking layout	Consecutive symbols each strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2

Physical data

Marker/strip width	5 mm
Marker width	5 mm

Mechanical data

Smear resistance	EN 60998-1:2004
------------------	-----------------

Material data

Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	7.8 g
Fire load	0.234 MJ

Commercial data

Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332102032
Customs tariff number	49119900000

Product Classification

UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 10.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 209-998

