

BZ-2RN784

[Products](#) > [Switches](#) > [Basic Switches](#) > [Premium Large Basic Switches](#) > [BZ Series](#) > [BZ-2RN784](#)

Overview

MICRO SWITCH BZ Series Premium Large Basic Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Overtravel Plunger Actuator, 2,5 N - 3.61 N [9 oz - 13 oz] Operating Force

[View More](#)



Technical Specifications

Switch Type	MICRO SWITCH Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]	Ampere Rating	15 A
		Circuitry	SPDT
		Termination	Screw
		Voltage	250 Vac
Sealed	No	Operating Force (OF)	2,5 N to 3,61 N [9.0 oz to 13.0 oz]
Actuator	Overtravel Plunger		
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]		
Contact Type	Silver		

[View More](#)

View documents in:

English ▾

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 BZ-2RN784 highres photo	Photo	English	1MB
 BZ-2RN784 lowres photo	Photo	English	59KB
 MICRO SWITCH BZ/BA/BM/BE & 6AS Series Premium Large Snap-Action Switches	Datasheet	English	2MB
 Oil and Gas Brochure	Brochure	English	4MB

[View More](#)

Product Features

- Accepted world-wide standard "Large Basic" switch
- Low operating force and differential travel
- Long mechanical life up to 20,000,000 cycles at 95% survival
- Elongated mounting hole for easier, more accurate mounting
- Current rating ranges from 15 A to 25 A
- Choice of actuation, termination and operating characteristics



view all BZ-2RN784 literature



view distributor inventory



sample request



email support



get support



email sales



find a distributor



email this page

Applications

- Irrigation systems
- Semi-trailer trucks
- Timing devices
- Office equipment
- Test instruments
- Medical/dental equipment
- HVAC equipment
- Manually operated devices
- Valves

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.