



1

2

3


4

5



Dimension:

POS.	Dim.A	Dim.B	POS.	Dim.A	Dim.B
2	2.50	7.50	9	20.00	25.00
3	5.00	10.00	10	22.50	27.50
4	7.50	12.50	11	25.00	30.00
5	10.00	15.00	12	27.50	32.50
6	12.50	17.50			
7	15.00	20.00			
8	17.50	22.50			



Specifications:

Current Rating:3.0A AC,DC

Voltage Rating:250V AC,DC

Contact Resistance:10mohm Max

Insulation Resistance:1000Mohm Min.

Withstanding Voltage:1000V AC/minute

Operating Temperature Range:-25°C~+85°C


Material And Finish:

Insulator:Nylon 66 (UL94V-0)

Insulator Color:White

Contact:Brass

Plated:Tin Plated



PCB Layout

RoHS Compliant

DRAWN:

GENERAL TOLERANCE:

.X=±0.20

.XX=±0.15

CHECKED:


UNIT: MM

SCALE:1:1

APPROVAL:

SHEET: 1 / 1

PROJECTION:



CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:

Wire-To Board Wafer
,2.5mm,Straight,Tin Plated,J Series

PART NO:

51025-XX-0100-01

SIZE

A4

REV

DATE

FILE

BY

17-Nov-2020