

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

KK03615200J0G

KK03615200J0G - Terminal Blocks : Pluggable plug, 10.16mm pitch, flange with screw, with handle, male plug, horizontal wire-inlet, 3 position



Customer drawing



Product Environmental Compliance Report

ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support
Sample request

Specifications

Download document

Mating Half

General	Dimensional	Electrical	Mechanical	Physical	Approvals / Certifications
General					
Gender					Male plug
Packaging					Box
Product Type					Screw Pluggable System
Series					KK
Number of Positions					3
Dimensional					
Strip length (Wire)					13 to 14 mm
Solid wire size (AWG)					6 to 20
Stranded wire size (AWG)					6 to 20
Pitch					10.16 mm
Screw Size					M4.5
Electrical					
Withstanding Voltage					2.2 kV
Current rating					55 A
Voltage rating					600 V
Mechanical					
Number of mating cycles					200
Physical					
Color (Housing)					Green
Conductor entry angle					0°
Material (Housing)					Thermoplastic UL94V-0
Terminal material					Copper
Terminal plating					Gold
Screw material					Steel
Screw plating					Zinc
Clamp material					Brass
Clamp plating					Nickel
Connection Type					Screw connection
Temperature (Operating - range)					-40 to 115 Celcius
Torque					18 Lb-in
Approvals / Certifications					
Approvals / Certifications					cULus

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.