


REVISIONS					
変更					
P	LTR	DESCRIPTION		DATE	APVD
	E	REVISED PER ECR-22-153759		10JUL2023	DZ

TYPE OF KEYING






注記

- 1. 一般公差 : ± 0.3
- 2. 材料PBTガラス強化(UL94V-0)
- 3. かん合相手製品型番
プラグハウジング : TABLE参照のこと
タブコンタクト : 917764,917765

NOTES

- 1. GENERAL TOLERANCE : ± 0.3
- 2. MATERIAL : PBT GRASS FILLED (UL94V-0)
- 3. MATING CONN. P/N
PLUG HOUSING : SEE TABLE
TAB CONTACT : 917764,917765



断面 A-A
SECT A-A

1-1981970-2	TYPE B	赤色 RED	1-1981971-2
1981970-1	TYPE A	自然色 NATURAL	1981971-1
3. かん合相手型番 MATING HSG P/N	キーイング形状 TYPE OF KEYING	色調 COLOR	型番 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SATO 02AUG2007	 TE Connectivity	
DIMENSIONS: 単位: 耗 mm		CHK S.MANABE 02AUG2007		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD S.MANABE 02AUG2007	NAME 名称	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格 108-78350	2.5MM PITCH CONN W-W WITH KEYING CAP HSG 8P	
MATERIAL 材料 SEE NOTE 2		APPLICATION SPEC 取付適用規格	SIZE A3	CAGE CODE 00779
FINISH 仕上		WEIGHT 0.000000	DRAWING NO 番号 C-1981971	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 尺度 4:1	SHEET 1 OF 1	REV E