



Overcome difficult connections due to confined spaces between a receiver and entertainment units, wall or rack with Velocity Right Angled Subwoofer cables.

Twisted pair oxygen-free copper wire and foamed PE dielectric fight noise and hum, and are optimized for bass signal transmission. Oxygen-free copper conductors deliver awesome impact and bass detail. The low loss 100% foil and spiral-wound oxygen-free copper (OFC) shielding protects the important bass signals from electromagnetic interference (EMI) and radio frequency interference (RFI). A tough, ultra-flexible jacket and 24K gold-plated heavy duty contacts ensure a lifetime of performance.

Features & Benefits

Oxygen-free copper center conductors	100% foil and dual OFC shields to protect against unwanted noise and interference
24K gold-plated contacts for long-lasting quality	

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120291800	Country Of Origin	Vietnam
Compliance	CE, RoHS	Application Sector	Commercial, Residential
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	12.0 FT	Cable Length	12 ft
-------------------	---------	--------------	-------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Signal Transmission	Bidirectional
Cable Type	Audio	Jacket Rating	Standard / Non-Rated
Cable Diameter	5.15 mm	Connector 2	RCA Line-level Audio Male

Connector 1	RCA Line-level Audio Male
-------------	---------------------------
