

5366-C



Straight Blade Plug, 20 Amp, 125 Volt, Industrial Grade - Black & White

20 Amp, 125 Volt, NEMA 5-20P, 2P, 3W, Plug, Straight Blade, Industrial Grade, Grounding - Black/White

Leviton's Black & White line of industrial grade plugs, connectors, flanged inlets, and outlets offer superior performance, long lasting reliability and features that are backed by a lifetime warranty:

- Captive, quick drive assembly screws for faster assembly
- Unique cord clamp accepts wide range of cord sizes (.245"-.700")
- Rugged nylon construction resists impact, heat, chemicals, and rough use
- Industry exclusive lifetime warranty
- Ideal for room air conditioners and generators

Color :  Black-White

UPC Code : 078477795873

Country Of Origin : Mexico

NEMA :  5-20P

Available Colors :



Technical Information

Environmental Specifications

Environment : Dry

Flammability : Rated HB or better UL94

Operating Temperature : -40° C to 60°C

Material Specifications

Assembly Screws : Steel, Zinc Plated

Back Cover : Thermoplastic

Blades/Contacts : Solid Brass

Body Material : Impact Modified Nylon

Clamp Insert : Nylon

Color : Black-White

Cord-Clamp : Nylon

Terminal Screws : Brass

Wire Module : Nylon

Mechanical Specifications

Amperage : 20 A

Cord Range : 0.230 to 0.685

Current Interrupting : Certified for current interrupting at full rated current

Dielectric Voltage : Withstands 2000V per UL498

Grounding : Grounding

Pole : 2

Product ID : Ratings and NEMA I.D. permanently marked on device

Product Features

Brand : Black and White

Color : Black-White

Device Type : Straight Blade Plug

NEMA : 5-20P

Temperature Rise : Max 30C
after 250 cycles OL at 200
percent rated current

Terminal Accom. : 18-10 AWG

Terminal ID : Brass-Hot,
Green-Ground, Silver-Neutral

Torque Range : 10-14 in-lbs

Voltage : 125 VAC

Wire : 3

Standards and Certifications

ANSI : C-73

CSA C22.2 No. 42 : File LR-406

NEMA : WD-6

NOM : 057

UL 498 : File E13399

UL Fed Spec WC-596 : File
E13393

Warranty : Limited Lifetime
Warranty Warranty

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	<input type="text"/>
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.

T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-461-2002 ·

FAX: +1-800-824-3005 ·

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)

5386- 1797 ·

Visit our Website at: www.leviton.com

© 2026 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/company/about-leviton/locations

© 2026 Leviton Manufacturing Co., Inc.