



Pushing Performance
Since 1945

har-key latching 90°



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 45 453 2302 |
| Specification | har-key latching 90° |
| HARTING eCatalogue | https://b2b.harting.com/09454532302 |

Identification

| | |
|---------------|---------------------|
| Category | Operator interfaces |
| Series | har-key |
| Element | Key switches |
| Specification | latching 90° |

Version

| | |
|-------------------------------|---|
| Diameter of the mounting hole | 30.5 mm |
| Details | This item requires additional contact blocks and a module holder to be functional. Please select these under “Matching Products”. |

Technical characteristics

| | |
|--|---------------------------------|
| Actuation path | 6 mm |
| Overvoltage category | III (protection by low voltage) |
| Tightening torque | ≤2.5 Nm Fixing nut |
| Operating temperature | -40 ... +70 °C |
| Storage temperature | -50 ... +85 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Isolation group | I (600 ≤ CTI) |
| Thickness of the panel | 1 ... 8 mm |

Material properties

| | |
|--------|--------|
| Colour | silver |
|--------|--------|



Pushing Performance
Since 1945

Specifications and approvals

| | |
|----------------|---|
| Specifications | EN 60947-5-1 |
| UL / CSA | UL 60947-5-1 NKCR.E534795 CSA C22.2 No. 60947-5-1:22 NKCR7.E534795 |

Commercial data

| | |
|--------------------------------|---------------|
| Packaging size | 10 |
| Net weight | 1 g |
| Country of origin | Germany |
| European customs tariff number | 85365080 |
| GTIN | 5713140449909 |
| ETIM | EC000222 |

Switching position

