

356/359 Screw Terminal Laminated Base Terminal for 3AG/AB Fuses



Dimensions



Fuse Type	A	B	C	D	E
3AG/3AB	See ordering information	2.38" [60.5 mm]	.25" [6.4 mm]	.91" [23.1 mm]	.73" [18.5 mm]

Additional Information

Datasheet 356 Series
Resources 356 Series
Samples 356 Series
Datasheet 359 Series
Resources 359 Series
Samples 359 Series

Product Characteristics

Compatible Fuse Size	3AG/AB
Electical	356 Series: 600 Vac/dc 15 A 359 Series: 600 Vac/dc 30 A
Clip/Terminals	356 000 Series: Nickel-plated spring brass 359 000 Series: Silver-plated beryllium copper
Terminals	B-32THD screw type
Base	Black phenolic laminate.
Mounting Hole	3AG Block: Reference Dimensions .142"/.147" [3.6/3.7 mm] diameter with .295"/.302" [7.5/7.7 mm] ×82" [20.8 mm] C.S.
Operation Temperature	-40 °C to +125 °C

Agency Approvals

Agency	Agency File Number
c UL us	E14721

Ordering Information

# of Poles	Dimension "A" [mm]	Ordering Number	
1	.78" [19.8]	**03560001Z**	**03590001Z**
2	1.69" [42.9]	**03560002Z**	**03590002Z**
3	2.59" [65.8]	**03560003Z**	**03590003Z**
4	3.50" [88.9]	**03560004Z**	**03590004Z**
5	4.41" [112.0]	**03560005Z**	**03590005Z**
6	5.31" [134.9]	**03560006Z**	**03590006Z**
7	6.21" [157.7]	**03560007Z**	**03590007Z**
8	7.12" [180.8]	**03560008Z**	**03590008Z**
9	8.03" [204.0]	**03560009Z**	**03590009Z**
10	8.94" [227.1]	**03560010Z**	**03590010Z**
11	9.84" [250.0]	**03560011Z**	**03590011Z**
12	10.75" [273.1]	**03560012Z**	**03590012Z**

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.

© 2021 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: 06/08/21

Downloaded from Arrow.com.