












				COLOR:GREEN	COLOR:BLUE	COLOR:RED	COLOR:BLACK	COLOR:NATURAL	
49.4	45.4	20.2	44	5054334276	5054334274	5054334272	5054334271	5054334270	42
49.4	45.4	20.2	44	5054334076	5054334074	5054334072	5054334071	5054334070	40
49.4	45.4	20.2	44	5054333876	5054333874	5054333872	5054333871	5054333870	38
49.4	45.4	20.2	44	5054333676	5054333674	5054333672	5054333671	5054333670	36
49.4	45.4	20.2	44	5054333476	5054333474	5054333472	5054333471	5054333470	34
49.4	45.4	20.2	44	5054333276	5054333274	5054333272	5054333271	5054333270	32
49.4	45.4	20.2	44	5054333076	5054333074	5054333072	5054333071	5054333070	30
49.4	45.4	20.2	44	5054332876	5054332874	5054332872	5054332871	5054332870	28
49.4	45.4	20.2	44	5054332676	5054332674	5054332672	5054332671	5054332670	26
37.4	33.4	14.2	32	5054332476	5054332474	5054332472	5054332471	5054332470	24
37.4	33.4	14.2	32	5054332276	5054332274	5054332272	5054332271	5054332270	22
37.4	33.4	14.2	32	5054332076	5054332074	5054332072	5054332071	5054332070	20
37.4	33.4	14.2	32	5054331876	5054331874	5054331872	5054331871	5054331870	18
37.4	33.4	14.2	32	5054331676	5054331674	5054331672	5054331671	5054331670	16
29.4	25.4	11.5	24	5054331476	5054331474	5054331472	5054331471	**5054331470**	**14**
29.4	25.4	11.5	24	5054331276	5054331274	5054331272	5054331271	5054331270	12
29.4	25.4	11.5	24	5054331076	5054331074	5054331072	5054331071	5054331070	10
29.4	25.4	11.5	24	5054330876	5054330874	5054330872	5054330871	5054330870	8
D	C	B	エンボステープ幅 WIDTH OF TAPE A	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	極数 CKT. NO
				オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	

NOTES

1. 製品番号505433**7*の詳細寸法は5054330002PSD000を参照ください。
   FOR DETAIL OF 505433**7* DIMENSIONS,
   PLEASE SEE THE 5054330002PSD000 (NOT PACKAGED).
2. 梱包数量　：　500個
   NUMBER OF CONNECTIORS : 500 PIECES/REEL.
3. リードテープ長さ
   LEAD TAPE LENGTH



4. 材料　MATERIAL
   キャリアテープ：ポリスチレン（PS）
   CARRIER TAPE : POLYSTYRENE (PS)
   トップテープ：ポリエステル（PET）、その他
   TOP TAPE : POLYESTER (PET) 、OTHER
   リール：ポリスチレン（PS）　<リサイクル材を含む>
   REEL : POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>

5. トップテープの剥離強度については、IEC60286-3に準拠
   TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED
EC NO: 112331 2017/02/08
DRWN: TAKAIKE 2017/03/30
CHK'D: KOMURAKAMI 2017/04/03
APPR: TKANEKO

REV: A

GENERAL TOLERANCES (UNLESS SPECIFIED)
ANGULAR TOL ± 3.0 °

4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS: MM
SCALE: NTS
DRWN BY: TAKAIKE DATE: 2017/02/08
CHK'D BY: KOMURAKAMI DATE: 2017/03/30
APPR BY: TKANEKO DATE: 2017/04/03
DRAWING SIZE: A3
THIRD ANGLE PROJECTION

molex®

MICRO-LOCK PLUS 1.25 W/B
DUAL ROW ST SMT EMBOSSED TAPE PKG

PRODUCT CUSTOMER DRAWING


SERIES	MATERIAL NUMBER	CUSTOMER
505433	SEE TABLE	GENERAL


DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
5054330001	PSD	000	1 OF 1


RELEASE STATUS	P1	RELEASE DATE	03.04.2017 04:16:58

FORMAT: master-lh.prod-A3
UNIT: 2013/12/14

Downloaded from Arrow.com.







NOTES

1. 嵌合相手：505432**0*
   MATE WITH : 505432**0*
2. 端子テール部 及び ネイルの平坦度：0.12MAX.
   TAIL AND NAIL COPLANARITY TO BE 0.12 MAX.
3. 極数 / 2 = 偶数に適用。
   APPLY FOR CKT. SIZE / 2 = EVEN.
4. 端子テール部に錫めっきを使用しているため、
   外観に摺動痕が付く場合が御座います。
   THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS BECAUSE THE TIN PLATING IS USED FOR THA TAIL.
5. 本製品のプラスチック部に黒点等が確認される場合や
   色合いが異なる場合がありますが、製品性能に影響はありません。
   THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH THE BLACK SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC PART OF THIS PRODUCT AND THE SHADE MIGHT BE DIFFERENT.
6. コネクタの詳細な取り扱いにつきましては、アプリケーション仕様書
   (AS-505432-001, -002)を参照して下さい。
   PLEASE REFER TO THE APPLICATION SPECIFICATION (AS-505432-001, -002)
   ABOUT THE DETAILED HANDLING OF THE CONNECTOR.
7. コネクタの仕様につきましては、
   製品仕様書(5054320000PS002)を参照して下さい。
   PLEASE REFER TO THE PRODUCT SPECIFICATION (5054320000PS002)
   ABOUT THE SPECIFICATION OF THE CONNECTOR.
8. オーダー番号と極数、色の関係
   RELATION ORDER NUMBER AND COLOR, CKT.

505433**7*
極数 CIRCUIT SIZE
色 COLOR

NO.	COLOR
0	NATURAL
1	BLACK
2	RED
4	BLUE
6	GREEN

※本製品はカバーテープ無し品です。
カバーテープ有り品は5054331000PSD000を参照してください。
THIS PRODUCT DON'T HAVE THE COVER TAPE. PLEASE REFER TO 5054331000PSD000 FOR THE PRODUCT WITH COVER TAPE.

C	B	A	HSG COLOR GREEN	HSG COLOR BLUE	HSG COLOR RED	HSG COLOR BLACK	HSG COLOR NATURAL	
25	26.25	30.85	5054334276	5054334274	5054334272	5054334271	5054334270	42
23.75	25	29.6	5054334076	5054334074	5054334072	5054334071	5054334070	40
22.5	23.75	28.35	5054333876	5054333874	5054333872	5054333871	5054333870	38
21.25	22.5	27.1	5054333676	5054333674	5054333672	5054333671	5054333670	36
20	21.25	25.85	5054333476	5054333474	5054333472	5054333471	5054333470	34
18.75	20	24.6	5054333276	5054333274	5054333272	5054333271	5054333270	32
17.5	18.75	23.35	5054333076	5054333074	5054333072	5054333071	5054333070	30
16.25	17.5	22.1	5054332876	5054332874	5054332872	5054332871	5054332870	28
15	16.25	20.85	5054332676	5054332674	5054332672	5054332671	5054332670	26
13.75	15	19.6	5054332476	5054332474	5054332472	5054332471	5054332470	24
12.5	13.75	18.35	5054332276	5054332274	5054332272	5054332271	5054332270	22
11.25	12.5	17.1	5054332076	5054332074	5054332072	5054332071	5054332070	20
10	11.25	15.85	5054331876	5054331874	5054331872	5054331871	5054331870	18
8.75	10	14.6	5054331676	5054331674	5054331672	5054331671	5054331670	16
7.5	8.75	13.35	5054331476	5054331474	5054331472	5054331471	5054331470	14
6.25	7.5	12.1	5054331276	5054331274	5054331272	5054331271	5054331270	12
5	6.25	10.85	5054331076	5054331074	5054331072	5054331071	5054331070	10
3.75	5	9.6	5054330876	5054330874	5054330872	5054330871	5054330870	8
			エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	エンボス梱包 EMBOSSED TAPE PACKAGE	極数 CKT. NO.
			オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	

PART	材質 MATERIAL
ハウジング HOUSING	ポリアミド(PA)　UL94V-0 色：表参照 POLY AMIDE(PA) UL94V-0 COLOR : SEE CHART
ターミナル及びネイル TERM AND NAIL	黄銅 BRASS
	錫ビスマスめっき：1.0 micro-meter MIN. TIN-BISMUTH PLATED
	ニッケルめっき（下地）：1.0 micro-meter MIN. NICKEL (UNDER PLATING)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED
EC NO: 112331
DRWN: TAKAIKE 2017/02/10
CHK'D: KOMURAKAMI 2017/03/30
APPR: TKANEKO 2017/04/03
A REV

GENERAL TOLERANCES (UNLESS SPECIFIED)
ANGULAR TOL ± 3.0 °
4 PLACES ± 0.2
3 PLACES ± 0.2
2 PLACES ± 0.2
1 PLACE ± 0.2
0 PLACES ± 0.2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS: MM　SCALE: 4:1
DRWN BY: TAKAIKE　DATE: 2017/02/10
CHK'D BY: KOMURAKAMI　DATE: 2017/03/30
APPR BY: TKANEKO　DATE: 2017/04/03
DRAWING SIZE: A3　THIRD ANGLE PROJECTION

molex®

MICRO-LOCK PLUS 1.25 W/B
DUAL ROW ST SMT PLUG ASSY

PRODUCT CUSTOMER DRAWING


SERIES	MATERIAL NUMBER	CUSTOMER
505433	SEE TABLE	GENERAL

DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
5054330002	PSD	000	1 OF 2


RELEASE STATUS	P1	RELEASE DATE	03.04.2017	04:16:59

FORMAT: molex-tb-wyd.A3
DATE: 2013/12/11
Downloaded from Arrow.com.


8-24 CKT. 係止形状
LOCK SHAPE OF 8-24 CKT.




26-32 CKT. 係止形状
LOCK SHAPE OF 26-32 CKT.




34-42 CKT. 係止形状
LOCK SHAPE OF 34-42 CKT.





嵌合状態図
MATED CONNECTORS



基板パターンレイアウト (参考)
(メタルマスク厚さ : 0.15mm)
RECCOMENDED P.C.B. PATTERN LAYOUT (REF.)
(METAL MASK THICKNESS : 0.15mm)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED
2017/02/10
2017/03/30
2017/04/03
EC NO: 112331
DRWN: TAKAIKE
CHK'D: KOMURAKAMI
APPR: TKANEKO

REV
A

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ±	3.0	°
4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS	SCALE
MM	4:1

DRWN BY	DATE
TAKAIKE	2017/02/10

CHK'D BY	DATE
KOMURAKAMI	2017/03/30

APPR BY	DATE
TKANEKO	2017/04/03

DRAWING SIZE: A3
THIRD ANGLE PROJECTION

molex®

MICRO-LOCK PLUS 1.25 W/B
DUAL ROW ST SMT PLUG ASSY

PRODUCT CUSTOMER DRAWING

SERIES	MATERIAL NUMBER	CUSTOMER
505433	SEE TABLE	GENERAL

DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
5054330002	PSD	000	2 OF 2

RELEASE STATUS	P1	RELEASE DATE	03.04.2017 04:16:59

Downloaded from Arrow.com.