
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.-.
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
H	—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST ISSUE	25JAN07	JL	BM







Loading Pattern (12 contacts)

	1	2	3	4	5	6	7
Row a	+	o	+	o	+	o	+
Row b	+	o	+	o	+	o	+
Row c	+	o	+	o	+	o	+


\+ = contact
o = no contact





Specifications acc. IEC 603-2. Performance Level 2

Housing :	PBTP 30% Glasfilled (UL94-V0) Pebblegrey similar RAL 7032
Contact material :	Copper Alloy
Plating :	Contact area : PdNi+Au or Au Termination area : Sn with flux-tight coating.



1 Center-displacement between termination- and contact-side.

Active Partnumber. Contact Tyco Electronics for other configuration availability

Old Partnumber	Tyco Part-number
V42254-F2299-R8	1982300-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± —
1 PLC	± 0,1
2 PLC	± 0,05
3 PLC	± —
4 PLC	± —
ANGLES	± 1

MATERIAL —
FINISH —

DWN	25JAN07 J.LOONEN
CHK	25JAN07 B.MOOIJ
APVD	25JAN07 J.BROEKSTEEG
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—

Tyco Electronics Corporation
's-Hertogenbosch,522AR-32

NAME: EUROCARD
RECEPTACLE ASS'Y, TYPE R21/12 POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-1982300-1	—

CUSTOMER DRAWING | SCALE 1:5 | SHEET 1 OF 1 | REV A

Downloaded from Arrow.com.