

Specification Sheet

Part Number: 113-00061



Reinforcement ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.

Simple one piece design for quick and easy installation.

Secures with a screw or bolt.

1-Piece Cable Tie with Screw Mount, 8.5" Long, 0.2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HS, Black, 1000/pkg

Article Number	113-00061
----------------	-----------

Type	T50MRX
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Screw Mount Cable Ties attach to existing holes using a screw or bolt to provide a fastening point to secure and route wire and cable bundles. Reinforced ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.
---------------------	--

Short Description	1-Piece Cable Tie with Screw Mount, 8.5" Long, 0.2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HS, Black, 1000/pkg
-------------------	--

Global Part Name	T50MRX-PA66HS-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.2
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Height H (Imperial)	.24

Height H (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.2 "
Mounting Hole Diameter D (Metric)	5.2 mm
Mounting Hole Diameter D Max (Metric)	5.2
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Plenum Rating	AH-2
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes

UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)