

[Germany](#) > ... > [Electrical products](#) > [Heat shrinkable tubing and ...](#) > [Thin-walled heat shrink ..](#) > GTI 3000 (3: 1) without flux ..**3M electrical products****Solutions for**

- Electrical installation
- energy networks
- industrial plants
- OEM
- train

New products

- Current

Do you already know...

- ACCR
- Heating tape application
- heating tape
- Insulating tapes and assembly tapes

Product Information

- general catalog

service

- Where to Buy
- Contact

[Where to Buy](#)

GTI 3000 (3: 1) without hot melt adhesive

description

Thin-walled heat shrink tubing made of polyolefin, for flexible, age-resistant insulation and color marking insulated electrically as well as it provides mechanical protection. The main application area is the electrical insulation and marking of connections on cables and lines, providing a smooth, glossy surface.

characteristics

- Shrinkage rate 3: 1
- Fast shrinking
- highly flexible
- Halogen free
- High resistance to aging

applications

For electrical insulation and marking of connections.

operating temperature

- 55 to + 135 ° C

Dielectric strength

35 kV / mm

longitudinal shrinkage

-5 max. %

minute shrink temperature

> = 120 ° C

shrink Ratio

3: 1

[write us](#)**Product Search** **product filter**[variants](#)[media](#)

Type no.	Ø before shrink	Ø according to shrink	Colour	length
GTI 3000 39/13 bk	39 mm	13 mm	black	1 m

Type no.	Ø before shrink	Ø according to shrink	Colour	length
GTI 3000 18/6 bk	18 mm	6 mm	black	1 m
GTI 3000 1.5 / 0.5 bk	1.5 mm	0.5 mm	black	1 m
GTI 3000 3/1 bk	3 mm	1 mm	black	1 m
GTI 3000 9/3 bk	9 mm	3 mm	black	1 m
GTI 3000 1.5 / 0.5 rd	1.5 mm	0.5 mm	red	1 m
GTI 3000 3/1 rd	3 mm	1 mm	red	1 m
GTI 3000 9/3 rd	9 mm	3 mm	red	1 m
GTI 3000 18/6 rd	18 mm	6 mm	red	1 m
GTI 3000 39/13 approx	39 mm	13 mm	red	1 m
GTI 3000 1.5 / 0.5 ye	1.5 mm	0.5 mm	yellow	1 m
GTI 3000 3/1 ye	3 mm	1 mm	yellow	1 m
GTI 3000 9/3 ye	9 mm	3 mm	yellow	1 m
GTI 3000 18/6 ye	18 mm	6 mm	yellow	1 m
GTI 3000 39/13 ye	39 mm	13 mm	yellow	1 m
GTI 3000 1.5 / 0.5 bl	1.5 mm	0.5 mm	blue	1 m
GTI 3000 3/1 bl	3 mm	1 mm	blue	1 m
GTI 3000 9/3 bl	9 mm	3 mm	blue	1 m
GTI 3000 18/6 bl	18 mm	6 mm	blue	1 m
GTI 3000 39/13 bl	39 mm	13 mm	blue	1 m
GTI 3000 1.5 / 0.5 wh	1.5 mm	0.5 mm	White	1 m
GTI 3000 3/1 wh	3 mm	1 mm	White	1 m
GTI 3000 9/3 wh	9 mm	3 mm	White	1 m
GTI 3000 18/6 wh	18 mm	6 mm	White	1 m
GTI 3000 39/13 wh	39 mm	13 mm	White	1 m
GTI 3000 1.5 / 0.5 clr	1.5 mm	0.5 mm	transparent	1 m

Type no.	Ø before shrink	Ø according to shrink	Colour	length
GTI 3000 3/1 clr	3 mm	1 mm	transparent	1 m
GTI 3000 9/3 clr	9 mm	3 mm	transparent	1 m
GTI 3000 18/6 clr	18 mm	6 mm	transparent	1 m
GTI 3000 39/13 clr	39 mm	13 mm	transparent	1 m
GTI 3000 1.5 / 0.5 br	1.5 mm	0.5 mm	brown	1 m
GTI 3000 3/1 br	3 mm	1 mm	brown	1 m
GTI 3000 9/3 br	9 mm	3 mm	brown	1 m
GTI 3000 18/6 br	18 mm	6 mm	brown	1 m
GTI 3000 39/13 br	39 mm	13 mm	brown	1 m
GTI 3000 6/2 bk	6 mm	2 mm	black	1 m
GTI 3000 24/8 bk	24 mm	8 mm	black	1 m
GTI 3000 6/2 rd	6 mm	2 mm	red	1 m
GTI 3000 6/2 ye	6 mm	2 mm	yellow	1 m
GTI 3000 6/2 bl	6 mm	2 mm	blue	1 m
GTI 3000 6/2 wh	6 mm	2 mm	White	1 m
GTI 3000 6/2 clr	6 mm	2 mm	transparent	1 m
GTI 3000 6/2 br	6 mm	2 mm	brown	1 m
GTI 3000 24/8 rd	24 mm	8 mm	red	1 m
GTI 3000 24/8 ye	24 mm	8 mm	yellow	1 m
GTI 3000 24/8 bl	24 mm	8 mm	blue	1 m
GTI 3000 24/8 wh	24 mm	8 mm	White	1 m
GTI 3000 24/8 clr	24 mm	8 mm	transparent	1 m
GTI 3000 24/8 br	24 mm	8 mm	brown	1 m

3M: [Press](#) | [Jobs and careers](#) | [Partner & Suppliers](#) | [Investor Relations](#) | [Advanced Search](#) | [Safety Data Sheets](#) | [SVHC Search](#) | [Contact 3M](#)

[Legal information and imprint](#) | [data protection](#) | [Cookie settings](#)

© 3M 2017. All rights reserved.

