



THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.







X(PANEL THICKNESS)	Y(CUTOUT DIMENSION)	Z(CUTOUT DIMENSION)
0.8~1.25 mm	27.3 $\pm^{0.2}_0$	31.4 $\pm^{0.5}_0$
1.25~2.0 mm	27.3 $\pm^{0.2}_0$	31.6 $\pm^{0.5}_0$

PANEL CUTOUT DIMENSION TABLE

NOTES:

RATING: 10A 250V AC
DUAL FUSEHOLDER, ONE ACTIVE, ONE SPARE
FUSES NOT INCLUDED - RECOMMENDED SIZE: 5 X 20mm
APPROVALS: UL,CSA,TUV,CCC
RoHS COMPLIANT



CONTROLLED

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Approvals	01-26-16	LY

8	Terminal Brass t=0.5mm	2
7	Terminal Brass t=0.8mm	1
6	Terminal Brass t=0.8mm	3
5	Terminal Copper t=2.0mm	2
4	Terminal Brass t=2.0mm	2
3	Terminal Brass t=2.0mm	1
2	Cover Nylon # 66 Color: Black	1
1	Case Nylon # 66 Color: Black	1

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION			
		Part Number: 723W-X2/04	RoHS Compliant		
0-1	0.15	Description: UNIVERSAL SNAP-IN INLET WITH FUSEHOLDER			
1-6	0.20				
6-18	0.30		UNIT: mm	REV. C	
18-50	0.50				
50-120	0.70		Drawn / Date	Checked / Date	Approved / Date
120-250	0.90		B.Zhang 04-04-05	04-04-05	JJH / 04-04-05
250-500	1.20				