

6

5

4

3

2







1

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/22/15	

APPROVED: _____

DATE: _____ TITLE: _____

DE09-HD-PX-TS



A

B

C

D

A

B

C

D

SPECIFICATIONS:

Material:

Insulator: ABS, rated UL 94HB

Hardware color: Black

Hardware: Steel, Chromate plated

Environmental:

Lead free, RoHS compliant

ADAM P/N	HOOD COLOR
DXXX-HD-PB-TS	BLACK PLASTIC
DXXX-HD-PN-TS	CHROME PLASTIC
DXXX-HD-PY-TS	GRAY PLASTIC

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

D-SUB HOOD, THUMB SCREWS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
.X	± .10	ØXX	± .10	SIZE	PART NO.	REV.	
.XX	± .020	ØXX	± .015	CHECKED	LL	5/22/15	
.XXX	± .015	ØXXX	± .010	DRAWN	HR	5/22/15	
APPROVALS				DATE			
APPROVED				REF: S00064T			
SCALE: NTS				SHEET 1 OF 5			



6

5

4

3

2





1

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				

APPROVED: _____

DATE: _____ TITLE: _____

DA15-HD-PX-TS



A

B

C

D

A

B

C

D

ADAM TECH909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB HOOD, THUMB SCREWS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES .X ± .10 .XX ± .020 .XXX ± .015				HOLES ØX ± .10 ØXX ± .015 ØXXX ± .010			
APPROVALS				DATE			
DRAWN				5/22/15			
CHECKED				5/22/15			
APPROVED				REV.			
SIZE				PART NO.			
X				DXXX-HD-PX-TS			
REF: S00064T				SCALE: NTS			
SHEET 2 OF 5				REV.			

6

5

4

3

2

1

6

5

4

3

2







1

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 5 FOR REVISION				

APPROVED: _____

DATE: _____ TITLE: _____

DB25-HD-PX-TS



A

B

C

D

A

B

C

D

ADAM TECH909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB HOOD, THUMB SCREWS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				Holes			
.X ± .10				ØX ± .10			
.XX ± .020				ØXX ± .015			
.XXX ± .015				ØXXX ± .010			
APPROVALS				DATE			
DRAWN	HR	5/22/15	SIZE	PART NO.	REV.		
CHECKED	LL	5/22/15	X	DXXX-HD-PX-TS	-		
APPROVED			REF: S00064T	SCALE: NTS	SHEET 3 OF 5		

6

5

4

3

2

1

6

5

4

3







2

1

APPROVED: _____

DATE: _____ TITLE: _____

DC37-HD-PX-TS

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	Holes
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

APPROVALS

APPROVALS	DATE
DRAWN AY	8/14/13
CHECKED AH	8/14/13
APPROVED	

ADAM TECH909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB HOOD, THUMB SCREWS

SIZE	PART NO.	REV.
X	DXXX-HD-PX-TS	-
REF: S00064T	SCALE: NTS	SHEET 4 OF 5

Rev AWO #

Description

Date

Appr

SEE SHT 1 OF 5 FOR REVISION

6

5

4

3

2





1

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 5 FOR REVISION				

APPROVED: _____

DATE: _____ TITLE: _____

DD50-HD-PX-TS

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES [MM]
TOLERANCES ARE AS NOTED

INCHES

HOLES

.X .10 ØX ±.10

.XX ±.020 ØXX ±.015

.XXX ±.015 ØXXX ±.010

APPROVALS

DATE

DRAWN

HR

5/22/15

CHECKED

LL

5/22/15

APPROVED

ADAM TECH909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE

D-SUB HOOD, THUMB SCREWS

SIZE

PART NO.

DXXX-HD-PX-TS

REV.

-

REF: S00064T

SCALE: NTS

SHEET 5 OF 5

A

B

C

D

A

B

C

D

6

5

4

3

2

1