

## FLPR8.0-SY



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Right Angle, 4.2mm. Dia. Low Profile Lens, 8.0in. Length, 3mm LED, Super Yellow

### FEATURES

### VALUE ADDED

### CHECK STOCK

- Wavelength: 590nm, Typical Intensity: 50mcd, Color: Yellow
- Assembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED
- 4.2mm. Diameter Low Profile Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Front Panel Mount Lens

[Enclosure Hardware](#)[LED Indicators](#)[LED Lighting](#)[New Products](#)[Locate a Distributor / Sales REP](#)[Quality Assurance / RoHS](#)[Product Info Center](#)[Terms & Conditions](#)[My Bivar](#)