Part Number : 640037970
Product Description : Square “DIN” style dies for 2 AWG
Series Number : 207126
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

ATS-638161100-001.pdf

ATS-640037970-001.pdf

TM-638161000-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207126
Description	Square “DIN” style dies for 2 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Crimp Module
UPC	884982831285
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
Pneumatic Universal Crimp Machine	638018900
Battery Powered Crimping Tool (115V)	638161000
Power Crimp Head for Din Style Crimp Dies	638161100

Applicable Parts

Description	Part Number
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 5/16" (M8), Tin Plated, Carton	192210237
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 3/8" (M9), Tin Plated, Carton	192210238
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 1/2" (M12), Tin Plated, Wide Pad, Carton	192210239
Compression Style Ring Tongue Terminal for 1 AWG Cable, Stud Size 3/8" (M9), Unplated, Carton	192210378
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 1/2" (M12), Unplated, Wide Pad, Carton	192210395
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 5/16" (M8), Unplated, Carton	192210396
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 1/4" (M6), Tin Plated, Carton	192210420
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 1/4" (M6), Unplated, Carton	192210421

Downloaded from Arrow.com.

Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 3/8" (M9), Unplated, Wide Pad, Carton	192210580
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 3/8" (M9), Tin Plated, Wide Pad, Carton	192210581
Compression Style Ring Tongue Terminal for 1 AWG Cable, Stud Size 10 (M5), Unplated, Carton	192210594
Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 10 (M5), Tin Plated, Carton	192210595
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton	191930297
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton	191930298
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton	191930299
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 3/4" (M18), Carton	191930320
VersaKrimp Parallel Splice for 2 AWG Wire, Carton	192050008
VersaKrimp Butt Splice for 2 AWG Wire, Carton	192150046
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/16" (M8), Tin Plated, Carton	192210233
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Tin Plated, Carton	192210235
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/2" (M12), Tin Plated, Wide Pad, Carton	192210236

Downloaded from Arrow.com.

Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Unplated, Carton	192210380
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/2" (M12), Unplated, Wide Pad, Carton	192210399
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/16" (M8), Unplated, Carton	192210400
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/4" (M6), Tin Plated, Carton	192210418
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/4" (M6), Unplated, Carton	192210419
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Unplated, Wide Pad, Carton	192210564
Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Tin Plated, Wide Pad, Carton	192210565
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton	191930296
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 7/16" (M11), Carton	191930302
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton	191930303
VersaKrimp Ring Tongue Terminal, 2 AWG, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton	191930305
VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton	191930307
VersaKrimp Ring Tongue Terminal	191930309

Downloaded from Arrow.com.

for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton	

Downloaded from Arrow.com.