



+ CONNECTORS

USB



✓ Active

TE CONNECTIVITY (TE)
USB CONN R/A SMT REC ASS'Y 4P

Universal Serial Bus | A

1-5353583-4
TE Internal Number: 1-5353583-4

EU RoHS Compliant
EU ELV Compliant

USB Type A
USB Version 2.0
Size Standard
Connector Style Receptacle
Number of Ports 1

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

RECEPTACLE ASS'Y R/A SMT STANDARD TYPE USB CONNECTOR

PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- USB Type A
- USB Version 2.0
- Size Standard
- Connector Style Receptacle
- Orientation Right Angle
- Connector & Contact Terminates To Printed Circuit Board
- LED Without
- Product Type Connector

Configuration Features

- Number of Ports 1
- Number of Positions 4
- Panel Ground With
- Panel Ground Type M2 Threaded Hole
- Panel Ground Location Right/Left

Body Features

- Shell Plating Finish Bright
- Shell Plating Material Tin

Contact Features

- Contact Mating Area Plating Thickness .76 μm [29.92 μin]
- Contact Mating Area Plating Material Gold or Gold Flash over Palladium Nickel

Termination Features

- Termination Method Solder
- Contact Termination Type Surface Mount

Mechanical Attachment

Locating Posts With
Mounting Location Top
Locking Feature Without
PCB Mount Retention Type SMT Hold-Down

Housing Features
Housing Color Black
Housing Material Thermoplastic

Dimensions
PCB Thickness (Recommended) 1 mm [.039 in]

Operation/Application
Pick and Place Pick and Place Cover

Industry Standards
Industry Standard USB 2.0

Packaging Features
Packaging Method Box & Tray, Tape
Packaging Quantity 55

PRODUCT COMPLIANCE

+

Statement of Compliance
Statement of Compliance
PDF