

Search within category

GO

BUY NOW

DESIGN / INSTALL



HSTT50-48-Q6

Thin wall heat shrink, .50" (12.7mm) diameter, black cross-linked polyolefin, blue, 25 pc. package quantity.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Product Type	Heat Shrink			
Material	Flame retardant polyolefin cross-linked except clear			
Color	Blue			
Shrink Ratio	2:1			
Temperature Range	-67°F - 275°F (-55°C - 135°C)			
Length (ft.)	4			
Length (m)	1.2			
Max. Recovered I.D. (In.)	0.250			
Max. Recovered I.D. (mm)	6.4			
Min. Expanded I.D. (In.)	0.500			
Min. Expanded I.D. (mm)	12.7			
Nominal Recovered Wall Thickness (In.)	0.025			
Nominal Recovered Wall Thickness (mm)	0.6			
Military Specification	AMS-DTL-23053/5 Class 1 (material performance only)			
UL Listed	No			
UL Recognized	Yes			
Flammability Rating	Flame Retardant			
Nominal Diameter / Size (mm)	12.7			
Sub Brand	Dry-Shrink			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	25			