




Part Number : [5006540619](#)
Product Description : 2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Crimp Type, 6 Circuits, Tray Packaging
Series Number : 500654
Status : Active
Product Category : I/O Connectors



Documents & Resources


Drawings
[5006540619_sd.pdf](#)

3D Models and Design Files
[5006540619_stp.zip](#)

Specifications
[5006540609AS-A00.pdf](#)
[5006549200-SPK-200.pdf](#)
[PS-500655-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 2-(2H-Benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol; Perfluorobutane sulfonic acid (PFBS) and its salts per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	500654
Description	2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Crimp Type, 6 Circuits, Tray Packaging
Application	Wire-to-Wire
Component Type	Plug
Product Name	2.00mm I/O Connectors
Type	N/A
UPC	191128798426

Electrical

Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	125V

Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black, Gray
Lock to Mating Part	Yes
Material - Metal	Stainless Steel
Material - Plating Mating	N/A
Material - Resin	Polycarbonate, Polyester
Net Weight	9073.064/mg

Orientation	Vertical
Packaging Type	Tray
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	N/A
Wire Insulation Diameter	1.20mm
Wire Size (AWG)	24, 26, 28

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.00mm Pitch IEEE 1394-1995 Shielded I/O PCB Socket, Right-Angle, Flat, Surface Mount, 6 Circuits, Tray Packaging	<u>534620629</u>
2.00mm Pitch Serial I/O Connector, Socket Kit, Wire-to-Wire Crimp Type, Without Flange, 6 Circuits	<u>5006550609</u>
2.00mm Pitch Serial I/O Connector, Socket Kit, Wire-to-Wire Crimp Type, With Flange, 6 Circuits	<u>5006550619</u>
2.00mm Pitch Serial I/O Connector, Receptacle Kit, Wire-to-Wire, Solder Type, 6 Circuits	<u>542800609</u>

Use with Part(s)

Description	Part Number
2.00mm Pitch Male Crimp Terminals	<u>50639</u>

This document was generated on Apr 26, 2025