

Part Number : 1300940438

Product Description : Standard Duty Support Grip, Locking Bale Eye, Split Rod, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1524.07kg (3360 lbs),



Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35337

Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Locking Bale Eye, Split Rod, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1524.07kg (3360 lbs),
Product Name	Standard Duty
Type	Support Grip
UPC	78678835337

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	1524.07kg (3360 lbs)
Bale Length	0.457m (18.00")
Body Style	Straight
Cable Diameter	50.80-63.25mm (2.000-2.490")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.559m (22.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 22, 2025