

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	16MAR2018	F.Z	R.B
	B	LOGO CHANGE; RESIN MARK ADD	08aug2018	F.Z	R.B
	C	REVISED PER ECR-24-207201	29APR2024	R.W	R.B

AS SHOWN

20POS(X-KEY) : 1-2333149-0

2Xn=A

2

3.3

CAVITY MARK
(ALPHABET:CAPITAL LETTER)

01 6 8 3 2 1

CIRCUIT NO.

D

KEYING : X

C

B

A

LOGO MARK

SERIES CODE

12.45±0.4

1.05

11.3

8.6

9.4

9

33PA9T B A

ROW ID

2

3.3

1.6

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.3, ±3°

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ±

FINISH -

MATERIAL

DWN
Fisher ZHU
29-Apr-24

CHK
Rick BIAN
29-Apr-24

APVD
Rick BIAN
29-Apr-24

PRODUCT SPEC
108-78268,78298

APPLICATION SPEC
114-5377

WEIGHT

Customer Drawing

DWN
Fisher ZHU
29-Apr-24

CHK
Rick BIAN
29-Apr-24

APVD
Rick BIAN
29-Apr-24

PRODUCT SPEC
108-78268,78298

APPLICATION SPEC
114-5377

WEIGHT

Customer Drawing

NAME
DYNAMIC D1100D 2.0mm PITCH
REC HSG
10-20 POS

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2333149

RESTRICTED TO

SCALE
4:1

SHEET
1

OF
3

REV
C

1. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. DIFFERENT HEIGHT OF LOCK PROTECTOR. A FINGERTIP IS STOOD AND PUSHED WHEN OPERATING A LOCK LEVER

Obsolete

20	X	9	18.0	20.9	22.6	6.8	1-2333149-0
18	X	8	16.0	18.9	20.6	8.1	1-2333149-9
10	X	4	8.0	10.9	12.6	3.6	1-2333149-5
10	X	4	8.0	10.9	12.6	3.6	9-2333149-5
POS	KEY	n	A	B	C	D	PART NO

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

CIRCUIT NO.

CAVITY MARK
(ALPHABET:CAPITAL LETTER)

LOGO MARK

SERIES CODE

KEYING MARK

ROW ID

LOGO MARK

SERIES CODE

KEYING MARK

CAVITY MARK
(ALPHABET:CAPITAL LETTER)


ROW ID

10POS(X-KEY)
1-2333149-5

10POS(X-KEY)
9-2333149-5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

DWN -
CHK -
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

Customer Drawing

STE

TE Connectivity

NAME
DYNAMIC D1100D 2.0mm PITCH
REC HSG
10-20 POS

SIZE A3 CAGE CODE 00779 DRAWING NO C-2333149

RESTRICTED TO -

SCALE 4:1

SHEET 2 OF 3

REV C

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

AS SHOWN

18POS(X-KEY) : 1-2333149-9

CIRCUIT NO.



CAVITY MARK
(ALPHABET:CAPITAL LETTER)

SERIES CODE

LOGO MARK


KEYING MARK

ROW ID



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

Customer Drawing



TE Connectivity

NAME

DYNAMIC D1100D 2.0mm PITCH
REC HSG
10-20 POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2333149

SCALE

4:1

SHEET

3

OF

3

REV

C