

CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, series: CA, angled, shielded: yes, SPEEDCON, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 4 mm ... 6 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1243529



Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1619411
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAED
Catalog page	Page 90 (C-2-2019)
GTIN	4046356824361
Weight per piece (including packing)	192.4 g
Weight per piece (excluding packing)	192.4 g
Customs tariff number	85366990
Country of origin	DE

CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Rated voltage	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overshoot category	III
Degree of pollution	3
Contact diameter Signal contacts	1 mm
Litz wire cross-section Signal contacts max.	1 mm ²
Nominal current per signal contact	8 A

Housing

Housing material	Metal
Type of locking	SPEEDCON
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	4 mm ... 6 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CA-12P1N12T006S - Cable connector


1619411

<https://www.phoenixcontact.com/us/products/1619411>



Drawings

Schematic diagram



Connector pin assignment


CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Dimensional drawing



Dimensional drawing

CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619411>

cUL Recognized		Approval ID: E335019-20141210	
		Nominal voltage U_N	Nominal current I_N
		48 V	6 A
			Cross section AWG
			- 18
			Cross section mm^2
			-

UL Recognized		Approval ID: E335019-20141210	
		Nominal voltage U_N	Nominal current I_N
		48 V	8 A
			Cross section AWG
			- 18
			Cross section mm^2
			-

cULus Recognized

CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Environmental product compliance

REACH SVHC

Lead 7439-92-1

China RoHS

Environmentally Friendly Use Period = 50 years

For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/us/products/1607456>

Torque screwdriver, series: RC



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/us/products/1607455>

Hook wrench, series: RC



CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/us/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/us/products/1620592>

Color coding, color: orange



CA-12P1N12T006S - Cable connector

1619411

<https://www.phoenixcontact.com/us/products/1619411>



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/us/products/1620593>

Color coding, color: black



PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/us/products/1577206>

Plastic protective cap, M23, degree of protection: IP20, series: CA



Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com