



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide
--------------------	--

## Physical

Colour	Black
Depth	34.3 cm
Height	8.3 cm
Net weight	10 kg
Width	21.6 cm

## Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

## Batteries & Runtime


Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge

Battery type	Lead-acid battery
Number of battery replacement quantity	1

## Packing Units

Package 1 Weight	10.91 kg
Package 1 Height	15.2 cm
Package 1 width	36.8 cm
Package 1 Length	49.5 cm
Number of Units in Package 3	20

## Offer Sustainability

Sustainable offer status	Green Premium product
Energy Star	<a href="#">ENERGY STAR UPS V1.0 (USA)</a> 
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------