



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL



GEE62FR-CY

Slotted grommet edging, .062" thickness, flame retardant polyethylene, natural, 100 ft.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Color	Natural
Flammability Rating	UL94V-0
Material	Flame Retardant Polyethylene
Maximum Compatible Panel Thickness (In.)	0.06
Maximum Compatible Panel Thickness (mm)	1.6
Maximum Operating Temperature (°C)	75
Maximum Operating Temperature (°F)	167
Minimum Compatible Panel Thickness (In.)	0.04
Minimum Compatible Panel Thickness (mm)	0.9
Minimum Operating Temperature (°C)	-20
Minimum Operating Temperature (°F)	-4
Overall Height (In.)	0.16
Overall Height (mm)	4.1
Overall Width (In.)	0.13
Overall Width (mm)	3.3
Overall Length (ft.)	100
Overall Length (m)	30.5
Standards Met	RoHS Compliant
Application	To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts.
Part Features	Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes.
RoHS Compliancy Status	Compliant
Min. Order Qty.	1