

Half Slim

SHE1B



GENERAL INFORMATION

TYPE	Half Slim	
INTERFACE	Serial ATA Revision 3.1	
DATA TRANSFER MODE	SATA 1.5Gbps, 3.0Gbps, 6.0Gbps	
CONNECTOR	15 + 7 pin Serial ATA	
OUTLINE DIMENSIONS	54 x 39 mm	
SERIES	SHE1B	
CONTROLLER TYPE	 TDK GBDriver GS1	
FLASH TYPE	SLC	pSLC/MLC
DENSITY RANGE	16 GB - 128 GB	pSLC:16GB-256GB MLC:32GB-512GB
DATA RETENTION	10 years @ life begin-10% 1 year @ life end	
ENDURANCE ENTERPRISE WL	100,000 P/E Cycles *Flash Block Level	pSLC:20,000P/ECycles MLC:3,000P/ECycles *Flash Block Level

TEMPERATURE

OPERATING TEMPERATURE	Commercial: 0°C to +70°C Industrial: -40°C to +85°C
STORAGE TEMPERATURE	Commercial: -25°C to +85°C Industrial: -40°C to +85°C

PERFORMANCE

Read (max.)	340 MByte/sec	pSLC:400 MByte/sec MLC:320 MByte/sec
Write (max.)	115 MByte/sec	pSLC:165 MByte/sec MLC:75 MByte/sec

ROBUSTNESS

MTBF	≥ 2,000,000 hours
SHOCK	1500G,0.5ms
VIBRATION	20G,10-2000Hz
HUMIDITY	0 to 90 % RH (No condensation)

ELECTRICAL DATA

VOLTAGE	5 V ± 10 %
POWER CONSUMPTION	- Read: 250mA max. - Write: 270mA max. - Slumber: less than 100mA

FEATURE LIST

FEATURES & TOOLS	- In-House Designed Controller (HW/FW) - Power Fail Data Safety - Power Back-up Circuit - Global static wear leveling - SMART - NCQ, TRIM - AES 128/256bit encryption	
PART NUMBER	SHE1BxxxxTXDxB00SSA0	SHE1BxxxxTxDxB00SSA0