

**May not be suitable for all medical and aerospace applications.**

**Specifications: Contact Mallory Sonalert to discuss your application.**

|                                |                                                 |
|--------------------------------|-------------------------------------------------|
| Oscillation Frequency (Hz)     | 3500 ± 500                                      |
| Operating Voltage (VDC)        | 3 ~ 28                                          |
| Rated Voltage (VDC)            | 12                                              |
| Current Consumption Max. (mA)  | 15 at Rated Voltage                             |
| Sound Pressure Level Min. (dB) | 90 at 30cm at Rated Voltage                     |
| Tone / Pulse Rate (Hz)         | Constant + Fast Pulse 3.0 ±20%                  |
| Operating Temperature (°C)     | -20 ~ +70                                       |
| Storage Temperature (°C)       | -30 ~ +80                                       |
| Housing                        | ABS 757 UL94 HB plastic resin<br>(Color: Black) |
| Leading Wire                   | 28 AWG                                          |
| Weight (Grams)                 | 7.8                                             |
| Options                        | For other options contact factory               |

**RoHS Compliant**

**Dimensions:** (units: mm)

Black to (-) and Red to (+) – Constant  
Blue to (-) and Red to (+) – Pulse

