



**Part Number :** [1062840001](#)

**Product Description :** CXP Optical Cable Assembly (iPass+ ), MTP-to-MTP, Multimode, 50/125µm, Round Cable Assembly, Straight Boot, Standard Bandwidth, OFNR, Cable Diameter 3.80mm, Cable Length 1.00m

**Series Number :** 86004

**Status :** Active

**Product Category :** Fiber Optic Cable Assemblies



---

## Documents and Resources


### Drawings

[1062840001\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86004
Description	CXP Optical Cable Assembly (iPass+ ), MTP-to-MTP, Multimode, 50/125µm, Round Cable Assembly, Straight Boot, Standard Bandwidth, OFNR, Cable Diameter 3.80mm, Cable Length 1.00m
Connector to Connector	MTP-to-MTP
Mode	Multimode
Product Name	CXP,iPass+,MTP
UPC	883906549237

### Physical

Boot Type	Straight
Cable Length	1.0m
Cable Size	3.80mm
Fiber (Core/Cladding)	50/125µm
Net Weight	34.144/g
Single Ended	No
Wire/Cable Type	Fiber Optic, Round

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	CXP Optical Transceivers

---

This document was generated on May 12, 2026