



1. PLUG : LT-550 AMERICAN TYPE
2. CONNECTOR : LT-549 IEC-60320 C19
3. CORD : SJT 12AWGX3C 105°C BLACK 4FT
4. APPROVALS : UL, C-UL
5. Supplier for flexible cord : RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

RHYTHM: (UL) E88231 SJT 3X12AWG(3.13mm)
105°C 300V VW-1 CSA LL54496 SJT
3X12AWG(3.13mm)105°C 300V VW-1
RHYTHM R

	DESCRIPTION	DATE

DRAWER	Eric	DATE	20/08/31	P/N	800-12-32D-BL-0004F-1
APPROVE		REV.	0	Dr.No.	1090755
		比例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

CnC Tech

Industrial Cable and Connector Technology