


Pushbutton, 9.1 mm, 1 NO, momentary contact function, 1 NO, bezel black



technical data

> general		direct links
Bezel color	black	
Property of bezel / mushroom	opaque	> RAFI eCatalog
Collar shape	round	
Operating temperature, min.	-25 °C	
Operating temperature, max.	70 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	80 °C	
illuminated	No	
Soldering time for manual soldering, max.	3 sec	
Soldering temperature for manual soldering	350 °C	
Soldering	Manual soldering	
Packaging	Box	
Packaging unit	10 pcs.	
Net weight	1.6 g	
Operating life	40,000 cycles	
B10	52,000 cycles	
Degree of protection, front side, according to DIN EN 60529	IP40	
Minimum order quantity (MOQ)	50 pcs.	
RoHS compliant	Yes	
REACH compliant	Yes	
Country of origin	HU	
> mounting diameters		
Outside dimension, length	11 mm	
Outside dimension, width	11 mm	
Outside dimension, height	30 mm	
Mounting hole	9.1 mm	
Mounting depth	25.5 mm	
Installation height	4.5 mm	

> **mechanical data**

Terminal on the rear	Solder terminal
Fixing	Threaded ring
Actuation function	momentary contact function
Operating force, max.	7 N
Operating force, min.	7 N
Operating travel, max.	2 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Solderability	Yes

> **electrical data**

Rated voltage, max.	24 V
Rated current, max.	0.1 A