



LMH 5mm 0.281"D Cable Assembly 0.5W 4"L

SKU: CNX_310_012_X_2_1_04

Category: [CNX 310 Series](#)**Description****Stock Availability****Technical Downloads**

Product Description

The CNX 310 series cable assemblies make quick and easy plug-in connections between panel mounted LEDs with lenses and a power source. Options include a broad selection of LEDs, choices of wire size, length and color, and a variety of wire terminations. With an integrated resistor, the CNX 310 series can be used on circuits from 3 to 28 volts. Panel thickness can vary from 1/32" to 1/4". The CNX 310 series is connected to the panel when coupled with a VCC press-fit lens.

Additional Information

Mounting Hole Dimension	<i>Dia. 0.281"</i>
LED Size	<i>5mm (T-1 3/4)</i>
Length Wire Leads	<i>4.0"</i>
Wire Gauge	<i>22 AWG</i>
RoHS	<i>Yes</i>
REACH Compliant	<i>Yes</i>
Conflict Mineral Free	<i>Yes</i>
Resistor	<i>120 ohm</i>

Plating	—
Style	—
LMH Angle	—
Connector with/with out wire	<i>Connector plus resistor & wire</i>
Pin Configuration	—
LMH Termination Wire	—
Termination	<i>Wirelead Ends Stripped</i>
Number of Circuits	—
Position	<i>One Position</i>

VCC CONTACT CAREERS WARRANTY POLICY TERMS & CONDITIONS PRIVACY & SECURITY STATEMENT



© 2015, 2016, 2017, 2018 Visual Communications Company, LLC
Contact Sales 1.800.522.5546

© 2015, 2016, 2017, 2018 Visual Communications Company, LLC



We use cookies to ensure that we give you the best experience on our website. Your continued use of the site constitutes your acceptance of this policy.

Ok